















# Armature Actuated Brakes ~ DC Direct Acting

[BACK TO AAB, SAB SELECTION PAGE](#)

## ARMATURE ACTUATED BRAKES (AAB)

|   |   |                |           | Page      |
|---|---|----------------|-----------|-----------|
|  | Introduction .....  |                |           | 61-62     |
|  | Selection .....   |                |           | 63        |
| Series  | Description   | Torque (lb-ft) | Nm        |           |
|  | 310 High Torque Holding Only - Servo Motor Brake                | 8 - 350 lb-in  | .9 - 39.5 | 64-65     |
|  | 311 High Torque Holding Only - Servo Motor Brake                | 75 - 400 lb-in | 8 - 45    | 66-67     |
|  | 320 Commercial Duty - Small Gear Motors                         | 3 - 50 lb-in   | .34 - 5.6 | 68-69     |
|  | 321/322 Totally-Enclosed, Non-Ventilated (TENV) Commercial Duty | 3 - 72 lb-in   | .34 - 8.1 | 70-73     |
|  | 321 NEMA C Totally-Enclosed, Non-Ventilated (TENV) C-Face Mount | 1.5 - 25 lb-ft | 2-34      | 74-75     |
|  | 331 & 333 European Style Metric Mounting                        | 3 - 300 lb-ft  | 4 - 400   | 76-78, 81 |
|  | 331 & 333 European Style - NEMA C-Face Mount                    | 3 - 300 lb-ft  | 4 - 400   | 79-81     |
|  | 350 European Style Portal Crane Duty - Pressure Plate Mount     | 75 - 300 lb-ft | 102 - 400 | 82-83     |
|  | 360 European Style Portal Crane Duty - Mag Body Mount           | 60 - 300 lb-ft | 80 - 400  | 84-85     |
|  | AAB Rectifiers .....  |                |           | 86-89     |
|  | Electronic Brake Release Indicator (Proving Switch) .....       |                |           | 90        |
|  | AAB Modification - Descriptions & Pricing .....                 |                |           | 91-93     |

## TECHNICAL DATA

|   |   |       |
|---|---|-------|
|    | Dimensions for C-Face AC Motors/Mounting Tolerances ..... | 96-97 |
|    | Conversions .....   | 99    |
|   | Set and Release Times .....                               | 98    |
|  | Formulas .....  | 129   |

## APPLICATION ENGINEERING ..... 118-128

This catalog is divided into sections for quick reference.  
 To open entire 136 page catalog [click here](#)...this may take several minutes to open.