

































Solenoid Actuated Brakes

[BACK TO AAB, SAB SELECTION PAGE](#)

SOLENOID ACTUATED BRAKES (SAB)					Page
	Introduction				3-7
	Selection				8
	Modifications - Descriptions and Prices				51-60
<hr/>					
CLOSE COUPLED (MOUNTED TO ACCESSORY END OF MOTOR)					
NEMA Frame	Series	Torque (lb-ft)	Nm	Enclosure	
	48C	48,100	1.5 - 6	2-8	IP 23 9
	56C - 145TC	56,X00	1.5 - 25	2-34	IP 21, 23, 54, 55, 56, 57 ... 10-15
	182TC - 256TC/UC	56,500	10 - 25	14-34	IP 23, 54, 55 16
	182TC - 256TC/UC	87,000	6 - 105	8-142	IP 23, 54, 55 17-19
	284TC/UC - 286TC/UC	87,100	50 - 105	68-142	IP 23, 54 20
	324 - 405TC/TSC/UC/USC	81,000	125 - 230	169-312	IP 23, 54 21-22
	324 - 405TC/TSC/UC/USC	82,000	125 - 440	169-597	IP 23, 54 21-23
	444 - 445TC/TSC/UC/USC	86,000	500 - 1,000	678-1356	IP 23, 54 24-25
	505TC/TSC/UC/USC	86,100	500 - 1,000	678-1356	IP 23, 54 24-25
<hr/>					
DIVISION 1 HAZARDOUS LOCATION					
	56C - 145TC	65,300	1.5 - 15	2-20	NEMA 7, 9 28-30
	182TC - 256TC/UC	87,300	10 - 105	14-142	NEMA 7, 9 31-34
	324 - 405 TC/TSC/UC/USC	82,300	125 - 330	169-447	NEMA 7, 9 35-36
	Foot Mounted	87,300	10 - 105	14-142	NEMA 7, 9 33-34
	Foot Mounted	82,300	125 - 330	169-447	NEMA 7, 9 36
<hr/>					
DIVISION 2 HAZARDOUS LOCATION					
	56C - 145TC	56,800	1.5 - 25	2-34	IP 56 37-38
	182TC - 256TC/UC	87,800	6 - 105	8 -142	IP 56 39-40
<hr/>					
DOUBLE C-FACE COUPLER BRAKES					
	56C - 145TC	56,700	1.5 - 25	2-34	IP 23, 54, 55, 56 41-42
	182TC - 256TC/UC	87,700	10 - 105	14-142	IP 23, 54, 55 43-44
<hr/>					
FOOT MOUNTED WITH BEARING SUPPORTED THRU SHAFT					
	Foot Mounted	56,700	1.5 - 25	2-34	IP 23 45
	Foot Mounted	87,200	10 - 105	14-142	IP 23, 54 46
<hr/>					
SPECIAL APPLICATION BRAKES					
	Marine/Maritime/Navy Applications				47
	Mining Brakes - MSHA Certified				48
	Encoder Brakes				49-50
<hr/>					
TECHNICAL DATA					
	Motor Frame Adapter Kits				94
	Foot Mounting Kits				95
	Dimensions for C-Face AC Motors/Mounting Tolerances				96-97
	Set and Release Times				98
	Conversions				99
	Formulas				129
<hr/>					
APPLICATION ENGINEERING					
					118-128

This catalog is divided into sections for quick reference.
 To open entire 136 page catalog [click here](#)...this may take several minutes to open.