

## Competitive Interchange List Armature Actuated Brakes NEMA Cface Motor Brakes

Lenze Interchange							
Lenze				Stearns			
Part Number	Mounting		Torque lb-ft (Nm)	Part Number	Mounting		Torque lb-ft (Nm)
	AJ	AK			AJ	AK	
4001	5.875	4.5	3 (4)	33C141G0	5.875	4.5	3 (4)
4002	5.875	4.5	6 (8)	33C241G0	5.875	4.5	6 (8)
4004	7.25	8.5	6 (8)	33C241H0	7.25	8.5	6 (8)
4003	5.875	4.5	12 (16)	33C341G0	5.875	4.5	12 (16)
4005	7.25	8.5	12 (16)	33C341H0	7.25	8.5	12 (16)
4006	7.25	8.5	25 (32)	33C441H0	7.25	8.5	25 (32)
4007	7.25	8.5	45 (60)	33C541H0	7.25	8.5	45 (60)
4008	7.25	8.5	60 (80)	33C641H0	7.25	8.5	60 (80)
4009	7.25	8.5	110 (150)	355744H0*	7.25	8.5	110 (150)
4010	9	10.5	180 (240)	355844J0*	9	10.5	180 (240)

\*The manual release on these models is internal only, maintained. Lenze manual release is external, non-maintained.

Kebco Interchange								
Kebco					Stearns			
Part Number		Mounting		Torque lb-ft (Nm)	Part Number	Mounting		Torque lb-ft (Nm)
Standard	Manual Release	AJ	AK			AJ	AK	
03.08.C10 -*60U 03.31.C10 -*60U	03.08.C30 -*60U 03.31.C30 -*60U	5.875	4.5	6 (8)	33C241G0	5.875	4.5	6 (8)
04.08.C10 -*60U 04.31.C10 -*60U	04.08.C30 -*60U 04.31.C30 -*60U	5.875	4.5	12 (16)	33C341G0	5.875	4.5	12 (16)
05.08.C10 -*80U 05.31.C10 -*80U	05.08.C30 -*80U 05.31.C30 -*80U	5.875	4.5	24 (32) 21 (28)	33C441G0	5.875	4.5	25 (32)
05.08.C10 -*A0U 05.31.C10 -*A0U	05.08.C30 -*A0U 05.31.C30 -*A0U	7.25	8.5	24 (32) 21 (28)	33C441H0	7.25	8.5	25 (32)
06.08.C10 -*A0U 06.31.C10 -*A0U	06.08.C30 -*60U 06.31.C30 -*60U	7.25	8.5	44 (60) 37 (50)	33C541H0	7.25	8.5	45 (60)
07.08.C10 -*B0U 07.31.C10 -*B0U	07.08.C30 -*60U 07.31.C30 -*60U	7.25	8.5	75 (102)	355734H0**	7.25	8.5	75 (102)
07.08.C10 -*D0U 07.31.C10 -*D0U	07.08.C30 -*D0U 07.31.C30 -*D0U	7.25	8.5	75 (102)	355734H0**	7.25	8.5	75 (102)
08.08.C10 -*D0U 08.31.C10 -*D0U	08.08.C30 -*D0U 08.31.C30 -*D0U	7.25	8.5	110 (150)	355744H0**	7.25	8.5	110 (150)
08.08.C10 -*F0U 08.31.C10 -*F0U	08.08.C30 -*F0U 08.31.C30 -*F0U	9	10.5	110 (150) 148 (200)	355744J0** 355844J0**	9	10.5	110 (150) 180 (240)

\*This digit indicates input voltage. 6 = 120 VAC, 7 = 230 VAC, 8 = 460 VAC

\*\*The manual release on these models is internal only, maintained. Kebco manual release is external, non-maintained.

## Stromag Interchange / Enclosed Brake

Stromag					Stearns					
Part Number	Mounting		Torque lb-ft (Nm)	Manual Release*	Part Number	Manual Release*	Mounting		Torque lb-ft (Nm)	Enclosure
	AJ	AK					AJ	AK		
SMB 2.5U	5.875	4.5	15 (20)	YES	33J434G0***R	YES	5.875	4.5	25 (34)	IP54
			37 (50)	NO	No Interchange	--			--	--
SMB 5U	7.25	8.5	35 (47)	YES	33J544H0***R	YES	7.25	8.5	45 (60)	IP54
			72 (98)	NO	355734H0***A	NO			75 (102)	IP56
SMB 10U	7.25	8.5	75 (102)	YES	355734H0***R	YES	7.25	8.5	75 (102)	IP56
			144 (195)	NO	355844H0***A	NO			180 (240)	IP56
SMB 20U	9.00	10.5	300 (400)	YES	355944J0***R	YES	9.00	10.5	300 (400)	IP56
			300 (400)	NO	355944J0***A	NO			300 (400)	IP56
SMB 30U	11.00	12.5	300 (400)	YES	355944K0***R	YES	11.00	12.5	300 (400)	IP56
			300 (400)	NO	355944K0***A	NO			300 (400)	IP56

\*The manual release on these Stearns models is internal only, maintained. Stromag manual release is external, non-maintained.

## Stromag Interchange / Cface only, no housing \*

Stromag					Stearns					
Part Number	Mounting		Torque lb-ft (Nm)	Manual Release	Part Number	Manual Release	Mounting		Torque lb-ft (Nm)	
	AJ	AK					AJ	AK		
SMB 2.5X	5.875	4.5	15 (20)	YES	333431G0***C	YES	5.875	4.5	25 (34)	
			37 (50)	NO	333541G0***A	NO			45 (60)	
SMB 5X	7.25	8.5	35 (47)	YES	333541H0***C	YES	7.25	8.5	45 (60)	
			72 (98)	NO	333731H0***C	NO			75 (102)	
SMB 10X	7.25	8.5	75 (102)	YES	333731H0***C	YES	7.25	8.5	75 (102)	
			144 (195)	NO	333841H0***A	NO			180 (240)	
SMB 20X	9.00	10.5	300 (400)	YES	333941J0***C	YES	9.00	10.5	300 (400)	
			300 (400)	NO	333941J0***A	NO			300 (400)	
SMB 30X	11.00	12.5	300 (400)	YES	333941K0***C	YES	11.00	12.5	300 (400)	
			300 (400)	NO	333941K0***A	NO			300 (400)	

\*Brake housings are available. If housing is required, contact factory.

With any interchange, request an outline drawing. Interchanges are based upon required torque and mounting dimensions only. Overall dimensions and materials may differ.

Kebco is a Registered Trademark of Kebco, Inc. or its affiliates.  
 Lenze is a Registered Trademark of Lenze Power Transmission or its affiliates.  
 Stromag Inc. is a Registered Trademark of Stromag, Inc or its affiliates.



Rexnord Industries, Inc.  
 Stearns Division  
 5150 S. International Dr.  
 Cudahy, Wisconsin 53110  
 Phone (414) 272-1100 Fax (414) 277-4364 [www.rexnord.com](http://www.rexnord.com)

Copyright © 2003 by Rexnord Industries, Inc. Printed in USA